



JAE320S-IP65

Technical Features

Electric current

| | |
|---|-------|
| Rated current | 200 A |
| Rated short-time withstand current Icw 1s IEC 60947 | 9 kA |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -5 - +40 °C |
|-----------------------|-------------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Voltage

| | |
|--------------------------------------|-------|
| Rated insulation voltage Ui | 800 V |
| Rated impulse withstand voltage Uimp | 8 V |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP65 |
|-------------------------------|------|

Dimensions

| | |
|--------|--------|
| Height | 600 mm |
| Width | 400 mm |
| Depth | 250 mm |

Installation, mounting

| | |
|-------------|---------------|
| Mounting on | Wall mounting |
|-------------|---------------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|