



IU36S

2 row, 36M din rail board, Surface

Technical Features

Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Surface mounting
-------------	------------------

Equipment

Number of rails	2
-----------------	---

Number of rows	2
----------------	---

Has neutral terminal block	Yes
----------------------------	-----

Capacity

Number of modules	36
-------------------	----

Dimensions

Height	380 mm
--------	--------

Width	475 mm
-------	--------

Depth	115 mm
-------	--------

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	110 mm
----------------	--------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	18
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Connection

Number of conduit inlets	4
--------------------------	---

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
----------	-------

RAL code	9002
----------	------

Colour	Grey white
--------	------------

Equipment

Has earthing terminal block	Yes
-----------------------------	-----

Has mounting plate	No
--------------------	----

Safety

Protection class	Isolation class I
------------------	-------------------

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP40
-------------------------------	------

Locking type	Without lock
--------------	--------------

Sustainability

REACH-SVHC free	Yes
-----------------	-----