



IU54S

**3 row, 54M din rail board, Surface**

**Technical Features**

**Voltage**

Nominal voltage	230 - 230 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Equipment**

Number of rails	3
Number of rows	3
Has neutral terminal block	Yes

**Capacity**

Number of modules	54
-------------------	----

**Dimensions**

Height	530 mm
Width	475 mm
Depth	115 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Built-in depth	110 mm
----------------	--------

**Cover, door**

Number of locks	0
-----------------	---

**Dimensions**

Number of width units	18
-----------------------	----

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Connection**

Number of conduit inlets	4
--------------------------	---

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Materials**

Material	Steel
RAL code	9002
Colour	Grey white

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP40
Locking type	Without lock

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----