



IU108S

6 row, 108M din rail board, Surface

Technical Features

Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Equipment

Number of rails	6
Number of rows	6
Has neutral terminal block	Yes

Capacity

Number of modules	108
-------------------	-----

Dimensions

Height	995 mm
Width	475 mm
Depth	115 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	110 mm
----------------	--------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	18
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Connection

Number of conduit inlets	4
--------------------------	---

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
RAL code	9002
Colour	Grey white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP40
Locking type	Without lock

Sustainability

REACH-SVHC free	Yes
-----------------	-----