



IU108S

### 6 row, 108M din rail board, Surface

#### Technical Features

##### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 230 - 230 V |
|-----------------|-------------|

##### Installation, mounting

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

##### Equipment

|                            |     |
|----------------------------|-----|
| Number of rails            | 6   |
| Number of rows             | 6   |
| Has neutral terminal block | Yes |

##### Capacity

|                   |     |
|-------------------|-----|
| Number of modules | 108 |
|-------------------|-----|

##### Dimensions

|        |        |
|--------|--------|
| Height | 995 mm |
| Width  | 475 mm |
| Depth  | 115 mm |

##### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

##### Dimensions

|                |        |
|----------------|--------|
| Built-in depth | 110 mm |
|----------------|--------|

##### Cover, door

|                 |   |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

##### Dimensions

|                       |    |
|-----------------------|----|
| Number of width units | 18 |
|-----------------------|----|

##### Cover, door

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

##### Connection

|                          |   |
|--------------------------|---|
| Number of conduit inlets | 4 |
|--------------------------|---|

##### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

##### Materials

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 9002       |
| Colour   | Grey white |

##### Equipment

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate          | No  |

##### Safety

|                               |                   |
|-------------------------------|-------------------|
| Protection class              | Isolation class I |
| Impact resistance IK          | IK05              |
| Ingress Protection (IP) class | IP40              |
| Locking type                  | Without lock      |

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|