



JAB306S-IP42

**Technical Features**

**Electric current**

Rated current	63 A
Rated short-time withstand current I <sub>cw</sub> 1s IEC 60947	1.5 kA

**Use conditions**

Operating temperature	-5 - +40 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated insulation voltage U <sub>i</sub>	800 V
Rated impulse withstand voltage U <sub>imp</sub>	8 V

**Safety**

Ingress Protection (IP) class	IP42
-------------------------------	------

**Dimensions**

Height	250 mm
Width	180 mm
Depth	105 mm

**Installation, mounting**

Mounting on	Wall mounting
-------------	---------------

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----