



JAE420S-IP65

Technical Features

Electric current

Rated current	200 A
Rated short-time withstand current Icw 1s IEC 60947	9 kA

Use conditions

Operating temperature	-5 - +40 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated insulation voltage Ui	800 V
Rated impulse withstand voltage Uimp	8 V

Safety

Ingress Protection (IP) class	IP65
-------------------------------	------

Dimensions

Height	600 mm
Width	400 mm
Depth	250 mm

Installation, mounting

Mounting on	Wall mounting
-------------	---------------

Sustainability

REACH-SVHC free	Yes
-----------------	-----