



JAB402S-IP42

### Technical Features

#### Electric current

Rated current	20 A
Rated short-time withstand current Icw 1s IEC 60947	1.26 kA

#### Use conditions

Operating temperature	-5 - +40 °C
-----------------------	-------------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Voltage

Rated insulation voltage Ui	800 V
Rated impulse withstand voltage Uimp	8 V

#### Safety

Ingress Protection (IP) class	IP42
-------------------------------	------

#### Dimensions

Height	250 mm
Width	180 mm
Depth	105 mm

#### Installation, mounting

Mounting on	Wall mounting
-------------	---------------

#### Sustainability

REACH-SVHC free	Yes
-----------------	-----