



JAB310S-IP65

Technical Features

Electric current

Rated current	100 A
Rated short-time withstand current Icw 1s IEC 60947	2.75 kA

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated insulation voltage Ui	800 V
Rated impulse withstand voltage Uimp	8 V

Safety

Ingress Protection (IP) class	IP65
-------------------------------	------

Dimensions

Height	300 mm
Width	300 mm
Depth	200 mm

Installation, mounting

Mounting on	Wall mounting
-------------	---------------

Sustainability

REACH-SVHC free	Yes
-----------------	-----