



XVR111C\_noir

**Charging station with one 1x07kW 1ph+N att. cable**

**Technical Features**

**Connection**

Connector/plug type	Type 2
---------------------	--------

**Connectivity**

Number of charging points	1
---------------------------	---

**Dimensions**

Depth	150 mm
Dimensions	370 x 250 mm
Height	370 mm
Width	250 mm

**Electric current**

Rated current	32 A
---------------	------

**Equipment**

Number of house sockets	0
With circuit breaker	No
With emergency release at power failure	Yes

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Functions**

With load management	No
----------------------	----

**Installation, mounting**

Mounting on	Wall mounting
-------------	---------------

**Materials**

Material	Plastic
----------	---------

**Power**

Connected load	0.1 - 7 kW
Power per charging point	7 kW

**Power supply**

Number of phases for power supply	1
-----------------------------------	---

**Safety**

Impact resistance IK	IK10
Ingress Protection (IP) class	IP55

**Use conditions**

Operating temperature	-25 - 50 °C
-----------------------	-------------

**Voltage**

Nominal voltage	230 - 230 V
-----------------	-------------

**Sustainability**

RoHS conform	Yes
--------------	-----