



47803515



Combination change-ov. sw./SCHUKO sock.outl. w. hing. cov. SM W1 grey

Technical Features

Dimensions

| | |
|------------------------------------|-------------|
| Dimensions | 147 x 76 mm |
| Built-in depth flush-mounted boxes | 0 mm |

Electric current

| | |
|-------------------|------|
| Rated current | 16 A |
| Switching current | 10 A |

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Materials

| | |
|--|---------------|
| Colour | Grey |
| RAL code | 7011 |
| Material | Thermoplastic |
| Surface finish | Matt |
| Contains recycled material (% of total plastic weight) | 29.9 % |

Safety

| | |
|----------------------------------|------|
| Ingress Protection (IP) class | IP55 |
| With enhanced contact protection | No |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -15 - 30 °C |
|-----------------------|-------------|

Equipment

| | |
|-----------------------------------|--------|
| With signal lamp | No |
| With round protective earth pin | No |
| Connector/plug type socket outlet | SCHUKO |
| Rotated central insert | No |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Texts

| | |
|--------------------|---|
| Installation mode | For vertical mounting |
| Protection | Without enhanced contact protection |
| Sealing | With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside |
| Type of connection | With plug-in terminals |

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
| RoHS conform | Yes |