



50753515



Push-button, 2 change-over contacts surf.-mtd, isol input term., W.1 ECO, gr m

Technical Features

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	Grey
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No
Contains recycled material (% of total plastic weight)	31.2 %

Dimensions

Height	55.90 mm
Width	55.90 mm
Depth	32.30 mm
Built-in depth flush-mounted boxes	0 mm

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Controls and indicators

Type of push button	Series push button
---------------------	--------------------

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-25 - 35 °C
-----------------------	-------------

Texts

Imprint	Without imprint
Installation mode	For screw fastening
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor
Type of connection	With plug-in terminals

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes