



47703525



### SCHUKO soc.out. 2gang vert. hinged cover surface-mtd, W.1, grey/light grey matt

#### Technical Features

##### Electric current

Rated current	16 A
---------------	------

##### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

##### Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Contains recycled material (% of total plastic weight)	27.7 %

##### Dimensions

Height	147 mm
Depth	65 mm
Built-in depth flush-mounted boxes	0 mm

##### Connection

Conductor cross-section	1.0 - 2.5 mm <sup>2</sup>
-------------------------	---------------------------

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

##### Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No
With lock	No

##### Accessories

Has labelling field	No
---------------------	----

##### Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

##### Capacity

Number of modules	2
-------------------	---

##### Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP55

---

**Functions**

With orientation lighting	No
With function lighting	No

**Texts**

Imprint	Without imprint
Cover	Complete housing
Wiring	Inserts wired-through
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

**Sustainability**

Halogen free	Yes
RoHS conform	Yes