



47753535



## SCHUKO soc. out. 2gang hor. hinged cover surface-mtd, W.1 ECO, grey matt

### Technical Features

#### Electric current

Rated current	16 A
---------------	------

#### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

#### Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Contains recycled material (% of total plastic weight)	27.7 %

#### Dimensions

Height	76 mm
Width	147 mm
Depth	63 mm
Built-in depth flush-mounted boxes	0 mm

#### Connection

Conductor cross-section	1.0 - 2.5 mm <sup>2</sup>
-------------------------	---------------------------

#### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

#### Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

#### Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No
With lock	No

#### Accessories

Has labelling field	Yes
---------------------	-----

#### Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

#### Capacity

Number of modules	2
-------------------	---

#### Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP55

# Product Datasheet

## 47753535

---

### Functions

With orientation lighting	No
With function lighting	No

### Texts

Imprint	Without imprint
Cover	Complete housing
Wiring	Inserts wired-through
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals
Labelling	With labelling field
Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor

### Sustainability

Halogen free	Yes
RoHS conform	Yes