



VR440EV

**4 Way 100A Switch disconnecter with 40A DP Switch Neutral RCBO**

**Technical Features**

**Installation, mounting**

Mounting on	Base
-------------	------

**Architecture**

Number of poles	2
-----------------	---

**Functions**

Has protection main switch	Yes
Overvoltage protection	No

**Installation, mounting**

Suitable for outdoor usage	No
----------------------------	----

**Configuration**

Number of arc fault detection devices AFDD	0
--	---

**Capacity**

Number of modules	4
-------------------	---

**Dimensions**

Depth	83 mm
Height	206 mm
Width	109 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	No

**Materials**

RAL code	9010
Colour	White
Material	Steel

**Connection**

Number of accessible phases	2
-----------------------------	---

**Scope of delivery**

Number of earth leakage circuit breaker type A	1
Number of RCCB in enclosure	1

**Equipment**

Number of groups	0
Number of light groups	0
Number of rows	1
With energy meter	No
Number of rails	0
Extension possible	No
With bell transformer	No
With socket outlet	No

**Safety**

Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Protection class	Isolation class III
Number of earth leakage switches 300 mA	0

**Compatibility**

Cooker group suitable as power current group	No
--	----

---

**Sustainability**

---

RoHS conform

Yes