



VR640EVSPD

### 6 Way 100A Switch disconnecter with 40A DP Switch Neutral RCBO+Type 2 Surge Prot

#### Technical Features

##### Installation, mounting

Mounting on	Base
-------------	------

##### Architecture

Number of poles	2
-----------------	---

##### Functions

Has protection main switch	Yes
Overvoltage protection	No

##### Configuration

Number of arc fault detection devices AFDD	0
--	---

##### Capacity

Number of modules	6
-------------------	---

##### Electric current

Rated current	100 A
---------------	-------

##### Dimensions

Depth	83 mm
Height	206 mm
Width	145 mm

##### Cover, door

Interlockable	No
Door/cover is transparent	No

##### Materials

RAL code	9010
Colour	White
Material	Metal

##### Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

##### Connection

Number of accessible phases	2
-----------------------------	---

##### Scope of delivery

Number of earth leakage circuit breaker type A	0
Number of RCCB in enclosure	1

##### Equipment

Number of groups	0
Number of light groups	0
Number of rows	1
With energy meter	No
Number of rails	0
Extension possible	No
With bell transformer	No

##### Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Protection class	Isolation class III

##### Sustainability

RoHS conform	Yes
--------------	-----