



WMSSU83/FAN

**13A FCU Switched Marked FAN**

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour White

Surface finish Glossy

Material Urea formaldehyde

Treatment Untreated

**Identification**

Assembly arrangement Basic element with full cover plate

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 86 x 86 mm

Built-in depth 25.30 mm

**Electric current**

Rated current 13 A

**Texts**

Installation mode For flush-mounted and hollow wall mounting

Lighting Without lighting (cannot be illuminated)

Push button No

Imprint With clear terminal markings

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes