



WMSSU83!HTG

**13A FCU Switched Marked HEATING**

**Technical Features**

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Urea formaldehyde
----------	-------------------

Treatment	Untreated
-----------	-----------

**Identification**

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Dimensions**

Dimensions	86 x 86 mm
------------	------------

Built-in depth	25.30 mm
----------------	----------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Electric current**

Rated current	13 A
---------------	------

**Texts**

Installation mode	For flush-mounted and hollow wall mounting
-------------------	--

Lighting	Without lighting (cannot be illuminated)
----------	--

Switch mode	2-pole
-------------	--------

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----