



WXF106

gallery socket mechanism compatible hidden and standard

Technical Features

Electric current

Rated current 16 A

Use conditions

Operating temperature -10 - +35 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour Dark grey

RAL code 7011

Surface finish Glossy

Material Polycarbonate (PC)

Dimensions

Height 45 mm

Width 45 mm

Depth 35.65 mm

Built-in depth flush-mounted boxes 40 mm

Installation, mounting

Mounting on Flush mounting
Trunking
Floor mounting

Equipment

Rotated central insert No

With hinged lid No

With round protective earth pin Yes

With signal lamp No

With lock No

Accessories

Has labelling field No

Pre-equipped with None

Capacity

Number of modules 2

Safety

With enhanced contact protection Yes

Impact resistance IK IK05

Ingress Protection (IP) class IP21

Identification

With imprint No

Suitable for

gallery

Sustainability

REACH-SVHC free Yes

RoHS conform Yes