



BD225

**Earth leakage add-on block 2P 25A 30mA A high immunity Class**

**Technical Features**

**Electric current**

Rated current	25 A
Rated residual operating current I <sub>dn</sub>	30 mA

**Architecture**

Number of poles	2
-----------------	---

**Safety**

Residual current type	A HI
-----------------------	------

**Capacity**

Number of modules	2
-------------------	---

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Power**

Total power loss under I <sub>N</sub>	3.1 W
---------------------------------------	-------

**Installation, mounting**

Nominal tightening torque	1.70 - 1.70 Nm
Nominal tightening torque down terminal	2.20 - 2.20 Nm

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

**Voltage**

Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V

**Dimensions**

Height	70 mm
Width	35 mm
Depth	92 mm

**Sustainability**

RoHS conform	Yes
--------------	-----

**Illustrations | Drawings**

