



BD225

Earth leakage add-on block 2P 25A 30mA A high immunity Class

Technical Features

Electric current

Rated current	25 A
Rated residual operating current I _{dn}	30 mA

Architecture

Number of poles	2
-----------------	---

Safety

Residual current type	A HI
-----------------------	------

Capacity

Number of modules	2
-------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

Total power loss under I _N	3.1 W
---------------------------------------	-------

Installation, mounting

Nominal tightening torque	1.70 - 1.70 Nm
Nominal tightening torque down terminal	2.20 - 2.20 Nm

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

Voltage

Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	4000 V

Dimensions

Height	70 mm
Width	35 mm
Depth	92 mm

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

