



BD225

Earth leakage add-on block 2P 25A 30mA A high immunity Class

Technical Features

Electric current	
Rated current	25 A
Rated residual operating current I _{dn}	30 mA
Architecture	
Number of poles	2
Safety	
Residual current type	A HI
Capacity	
Number of modules	2
Frequency	
Frequency	50 - 50 Hz
Installation, mounting	
Nominal tightening torque	1.70 - 1.70 Nm
Power	
Total power loss under I _N	3.1 W
Endurance	
Electric endurance in number of cycles	2000
Number of mechanical operations	2000
Voltage	
Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	4000 V
Dimensions	
Height	70 mm
Width	35 mm
Depth	92 mm
Sustainability	
RoHS conform	Yes

Illustrations | Drawings

