



BD226N

**Earth leakage add-on block 2P 25A 30mA AC Class**

**Technical Features**

**Architecture**

Neutral position	Right
Number of poles	2

**Capacity**

Number of modules	2
-------------------	---

**Voltage**

Rated operational voltage $U_e$	230 - 230 V
Rated insulation voltage $U_i$	500 V
Rated impulse withstand voltage $U_{imp}$	4000 V

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Electric current**

Rated residual operating current $I_{dn}$	30 mA
Rated current	25 A

**Connectivity**

Down connection alignment for modular devices	Aligned terminal
---	------------------

**Installation, mounting**

Nominal tightening torque	2.20 - 2.20 Nm
Nominal tightening torque down terminal	2.20 - 2.20 Nm

**Dimensions**

Height	70 mm
Width	35 mm
Depth	92 mm

**Sustainability**

RoHS conform	Yes
--------------	-----