



BD241

Earth leakage add-on block 2P 40A 30mA AC Class

Technical Features

Architecture

Number of poles 2

Capacity

Number of modules 2

Voltage

Rated insulation voltage U_i 500 V

Rated impulse withstand voltage U_{imp} 4000 V

Frequency

Frequency 50 - 50 Hz

Electric current

Rated residual operating current I_{dn} 30 mA

Rated current 40 A

Installation, mounting

Nominal tightening torque 2.80 - 2.80 Nm

Nominal tightening torque down terminal 2.90 - 2.90 Nm

Sustainability

RoHS conform Yes

Illustrations | Drawings

