



BD325

Earth leakage add-on block 3P 25A 30mA A high immunity Class

Technical Features

Electric current

Rated current	25 A
Rated residual operating current I_{dn}	30 mA

Architecture

Number of poles	3
-----------------	---

Safety

Residual current type	A HI
-----------------------	------

Capacity

Number of modules	2
-------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	1.70 - 1.70 Nm
---------------------------	----------------

Power

Total power loss under I_N	5 W
------------------------------	-----

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

Voltage

Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

