



BD425N

Earth leakage add-on block 4P 25A 30mA A Class

Technical Features

Voltage

Rated operational voltage $U_e$	230 - 400 V
Rated insulation voltage $U_i$	500 V
Rated impulse withstand voltage $U_{imp}$	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current $I_{dn}$	30 mA
Rated current	25 A

Architecture

Number of poles	4
Neutral position	Right

Dimensions

Height	70 mm
Width	44 mm
Depth	92 mm

Sustainability

RoHS conform	Yes
--------------	-----