



BD464

Earth leakage add-on block 4P 63A 30mA AC Class

Technical Features

Architecture

Neutral position	Left
Number of poles	4

Capacity

Number of modules	3
-------------------	---

Voltage

Rated operational voltage U_e	230 - 400 V
Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current I_{dn}	30 mA
Rated current	63 A

Sustainability

RoHS conform	Yes
--------------	-----