



BDC840

Earth leakage add-on-block with double output 4P 25A 30mA A high immunity class

Technical Features

<b>Electric current</b>	
Rated current	25 A
Rated residual operating current I <sub>dn</sub>	30 mA
<b>Architecture</b>	
Number of poles	4
<b>Safety</b>	
Residual current type	A HI
<b>Capacity</b>	
Number of modules	3
<b>Frequency</b>	
Frequency	50 - 50 Hz
<b>Installation, mounting</b>	
Nominal tightening torque	1.70 - 1.70 Nm
<b>Power</b>	
Total power loss under I <sub>N</sub>	1.7 W
<b>Endurance</b>	
Electric endurance in number of cycles	1000
Number of mechanical operations	6000
<b>Voltage</b>	
Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V
<b>Connectivity</b>	
Down connection alignment for modular devices	Aligned terminal
<b>Dimensions</b>	
Height	102 mm
Width	52.50 mm
Depth	70 mm
<b>Sustainability</b>	
RoHS conform	Yes

Illustrations | Drawings

