



BE464

Earth leakage add-on block 4P 63A 100mA AC Class

Technical Features

Architecture

|                  |      |
|------------------|------|
| Neutral position | Left |
| Number of poles  | 4    |

Voltage

|   |             |
|---|-------------|
| Rated operational voltage $U_e$           | 230 - 400 V |
| Rated insulation voltage $U_i$            | 500 V       |
| Rated impulse withstand voltage $U_{imp}$ | 4000 V      |

Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Electric current

|   |        |
|---|--------|
| Rated residual operating current $I_{dn}$ | 100 mA |
| Rated current                             | 63 A   |

Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|