



BE464

Earth leakage add-on block 4P 63A 100mA AC Class

Technical Features

Architecture

Neutral position	Left
Number of poles	4

Voltage

Rated operational voltage Ue	230 - 400 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current Idn	100 mA
Rated current	63 A

Sustainability

RoHS conform	Yes
--------------	-----