



BF225

Earth leakage add-on block 2P 25A 300mA A high immunity Class

Technical Features

<b>Electric current</b>	
Rated current	25 A
Rated residual operating current I <sub>dn</sub>	300 mA
<b>Architecture</b>	
Number of poles	2
<b>Safety</b>	
Residual current type	A HI
<b>Capacity</b>	
Number of modules	2
<b>Frequency</b>	
Frequency	50 - 50 Hz
<b>Installation, mounting</b>	
Nominal tightening torque	1.70 - 1.70 Nm
<b>Power</b>	
Total power loss under I <sub>N</sub>	2 W
<b>Endurance</b>	
Electric endurance in number of cycles	2000
Number of mechanical operations	2000
<b>Voltage</b>	
Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V
<b>Sustainability</b>	
RoHS conform	Yes

Illustrations | Drawings

