



BF241

**Earth leakage add-on block 2P 40A 300mA AC Class**

**Technical Features**

**Architecture**

|                  |      |
|------------------|------|
| Neutral position | Left |
| Number of poles  | 2    |

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

**Voltage**

|   |             |
|---|-------------|
| Rated operational voltage $U_e$           | 230 - 400 V |
| Rated insulation voltage $U_i$            | 500 V       |
| Rated impulse withstand voltage $U_{imp}$ | 4000 V      |

**Electric current**

|   |        |
|---|--------|
| Rated residual operating current $I_{dn}$ | 300 mA |
| Rated current                             | 40 A   |

**Installation, mounting**

|   |                |
|---|----------------|
| Nominal tightening torque               | 2.80 - 2.80 Nm |
| Nominal tightening torque down terminal | 2.90 - 2.90 Nm |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

**Illustrations | Drawings**

