



BF326

Earth leakage add-on block 3P 25A 300mA AC Class

Technical Features

Architecture

Neutral position	Left
Number of poles	3

Capacity

Number of modules	2
-------------------	---

Voltage

Rated operational voltage U_e	230 - 400 V
Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current I_{dn}	300 mA
Rated current	25 A

Installation, mounting

Nominal tightening torque	1.70 - 1.70 Nm
Nominal tightening torque down terminal	2.20 - 2.20 Nm

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

