



BF263

**Earth leakage add-on block 2P 63A 300mA A high immunity Class**

**Technical Features**

**Electric current**

Rated current	63 A
Rated residual operating current I <sub>dn</sub>	300 mA

**Architecture**

Number of poles	2
-----------------	---

**Safety**

Residual current type	A HI
-----------------------	------

**Capacity**

Number of modules	2
-------------------	---

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Power**

Total power loss under I <sub>N</sub>	4.4 W
---------------------------------------	-------

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.90 - 2.90 Nm

**Endurance**

Electric endurance in number of cycles	2000
--	------

**Voltage**

Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V

**Sustainability**

RoHS conform	Yes
--------------	-----

**Illustrations | Drawings**

