



BF363

Earth leakage add-on block 3P 63A 300mA A high immunity Class

Technical Features

Electric current

Rated current	63 A
Rated residual operating current I _{dn}	300 mA

Architecture

Number of poles	3
-----------------	---

Safety

Residual current type	A HI
-----------------------	------

Capacity

Number of modules	3
-------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
---------------------------	----------------

Power

Total power loss under I _N	9.7 W
---------------------------------------	-------

Endurance

Electric endurance in number of cycles	2000
--	------

Voltage

Rated insulation voltage U _i	500 V
Rated impulse withstand voltage U _{imp}	4000 V

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

