



BF364

Earth leakage add-on block 3P 63A 300mA AC Class

Technical Features

Architecture

Neutral position	Left
Number of poles	3

Capacity

Number of modules	3
-------------------	---

Voltage

Rated operational voltage Ue	230 - 400 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current Idn	300 mA
Rated current	63 A

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

