



BFC825

Earth leakage add-on-block with double output 4P 25A 300mA AC class

Technical Features

Architecture

Neutral position	Left
Number of poles	4

Capacity

Number of modules	3
-------------------	---

Voltage

Rated operational voltage U_e	230 - 400 V
Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current I_{dn}	300 mA
Rated current	25 A

Connectivity

Down connection alignment for modular devices	Aligned terminal
---	------------------

Dimensions

Height	102 mm
Width	52.50 mm
Depth	70 mm

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

