



BF441

**Earth leakage add-on block 4P 40A 300mA AC Class**

**Technical Features**

**Architecture**

Neutral position	Left
Number of poles	4

**Capacity**

Number of modules	3
-------------------	---

**Voltage**

Rated operational voltage Ue	230 - 400 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Electric current**

Rated residual operating current Idn	300 mA
Rated current	40 A

**Sustainability**

RoHS conform	Yes
--------------	-----