



BDC840

**Earth leakage add-on-block with double output 4P 25A 300mA A high immunity class**

**Technical Features**

**Electric current**

Rated current	25 A
Rated residual operating current $I_{dn}$	300 mA

**Architecture**

Number of poles	4
-----------------	---

**Safety**

Residual current type	A HI
-----------------------	------

**Capacity**

Number of modules	3
-------------------	---

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Power**

Total power loss under $I_N$	1.7 W
------------------------------	-------

**Endurance**

Electric endurance in number of cycles	1000
Number of mechanical operations	6000

**Voltage**

Rated insulation voltage $U_i$	500 V
Rated impulse withstand voltage $U_{imp}$	4000 V

**Connectivity**

Down connection alignment for modular devices	Aligned terminal
---	------------------

**Dimensions**

Height	102 mm
Width	52.50 mm
Depth	70 mm

**Sustainability**

RoHS conform	Yes
--------------	-----

**Illustrations | Drawings**

