



BDC840

Earth leakage add-on-block with double output 4P 63A 300mA high immunity class

Technical Features

Electric current

Rated current	63 A
Rated residual operating current I_{dn}	300 mA

Architecture

Number of poles	4
-----------------	---

Safety

Residual current type	A HI
-----------------------	------

Capacity

Number of modules	3
-------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

Total power loss under I_N	11.2 W
------------------------------	--------

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	6000

Voltage

Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V

Connectivity

Down connection alignment for modular devices	Aligned terminal
---	------------------

Dimensions

Height	102 mm
Width	52.50 mm
Depth	70 mm

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

