



BG464

**Earth leakage add-on block 4P 63A 500mA AC Class**

**Technical Features**

**Architecture**

Neutral position	Left
Number of poles	4

**Voltage**

Rated operational voltage $U_e$	230 - 400 V
Rated insulation voltage $U_i$	500 V
Rated impulse withstand voltage $U_{imp}$	4000 V

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Electric current**

Rated residual operating current $I_{dn}$	500 mA
Rated current	63 A

**Connectivity**

Down connection alignment for modular devices	Aligned terminal
---	------------------

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.90 - 2.90 Nm

**Dimensions**

Height	70 mm
Width	78 mm
Depth	83 mm

**Sustainability**

RoHS conform	Yes
--------------	-----