



BP464N

Earth leakage add-on block 4P 63A 300mA AC S Class

Technical Features

Voltage

| | |
|---|-------------|
| Rated operational voltage U_e | 230 - 400 V |
| Rated insulation voltage U_i | 500 V |
| Rated impulse withstand voltage U_{imp} | 4000 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Electric current

| | |
|---|--------|
| Rated residual operating current I_{dn} | 300 mA |
| Rated current | 63 A |

Architecture

| | |
|------------------|-------|
| Number of poles | 4 |
| Neutral position | Right |

Capacity

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Installation, mounting

| | |
|---|----------------|
| Nominal tightening torque | 2.90 - 2.90 Nm |
| Nominal tightening torque down terminal | 2.90 - 2.90 Nm |

Connectivity

| | |
|---|------------------|
| Down connection alignment for modular devices | Aligned terminal |
|---|------------------|

Dimensions

| | |
|--------|-------|
| Height | 70 mm |
| Width | 35 mm |
| Depth | 92 mm |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|