



BDC840

Earth leakage add-on block 4P 63A 1A AC S Class

Technical Features

Voltage

Rated operational voltage Ue	230 - 400 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current I <sub>dn</sub>	1000 mA
Rated current	63 A

Architecture

Number of poles	4
Neutral position	Left

Capacity

Number of modules	3
-------------------	---

Sustainability

RoHS conform	Yes
--------------	-----