



KDN380B

Insulated busbar 3P 80A fork 16mm² 57M

Technical Features

Electric current

Rated current I _N	80 A
------------------------------	------

Architecture

Number of poles	3
Type of pole	3P

Dimensions

Length	1000 mm
--------	---------

Voltage

Rated impulse withstand voltage U _{imp}	4500 V
Rated operational voltage U _e	230 - 400 V

Connection

Cross-section rigid conductor	16 mm ²
Connector/plug type	Phase busbar with fork

Capacity

Number of modules	57
-------------------	----

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes