



Technical Features

Rated current	80 A
---------------	------

Number of poles	4
-----------------	---

Type of pole	3x 1P+N
--------------	---------

Length 1000 mm

Rated impulse withstand voltage U_{imp}	4500 V
---	--------

Rated operational voltage U_e	230 - 400 V
---------------------------------	-------------

Cross-section rigid conductor	16 mm ²
-------------------------------	--------------------

Connector/plug type	Phase busbar with fork
---------------------	------------------------

Number of modules	54
-------------------	----

Halogen free	Yes
--------------	-----

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----