




KDN363B

Insulated busbar 3P 63A fork 10mm² 57M

Technical Features

Electric current

Rated current	63 A
---------------	------

Architecture

Number of poles	3
Type of pole	3P

Dimensions

Length	1000 mm
--------	---------

Voltage

Rated impulse withstand voltage Uimp	4500 V
Rated operational voltage Ue	230 - 400 V

Connection

Cross-section rigid conductor	10 mm ²
Connector/plug type	Phase busbar with fork

Capacity

Number of modules	57
-------------------	----

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes