

#### Technical Features

##### Installation, mounting

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

##### Electric current

|               |       |
|---------------|-------|
| Rated current | 400 A |
|---------------|-------|

##### Equipment

|                             |     |
|-----------------------------|-----|
| With lock                   | Yes |
| Has neutral terminal block  | Yes |
| Has earthing terminal block | Yes |
| Has mounting plate          | Yes |

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

##### Dimensions

|        |        |
|--------|--------|
| Height | 770 mm |
| Width  | 770 mm |
| Depth  | 220 mm |

##### Cover, door

|                           |    |
|---------------------------|----|
| Number of cabinet doors   | 1  |
| Door/cover is transparent | No |

##### Materials

|          |            |
|----------|------------|
| Material | Metal      |
| RAL code | 7035       |
| Colour   | Light grey |

##### Safety

|                               |                   |
|-------------------------------|-------------------|
| Protection class              | Isolation class I |
| Impact resistance IK          | IK10              |
| Ingress Protection (IP) class | IP42              |
| Locking type                  | Key lock          |