



Silhouette 1G LP electronic Switch Vert

Technical Features

Frequency

Frequency 50 - 50 Hz

Power

Power consumption standby 0.35 W

230 V incandescent and halogen lamp 1200 W

Use conditions

Operating temperature 5 - 40 °C

Dimensions

Built-in depth 47 mm

Texts

Extension unit input With extension unit input for slave push-button WBMESL

Installation mode For screw fastening

Type of connection With screw terminals

Sustainability

Halogen free Yes

RoHS conform Yes

WBSEV1

