



Silhouette 1G LP electronic Switch Vert

Technical Features

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

Power consumption standby	0.35 W
---------------------------	--------

230 V incandescent and halogen lamp	1200 W
-------------------------------------	--------

Use conditions

Operating temperature	5 - 40 °C
-----------------------	-----------

Dimensions

Built-in depth	47 mm
----------------	-------

Texts

Extension unit input	With extension unit input for slave push-button WBMESL
----------------------	--

Installation mode	For screw fastening
-------------------	---------------------

Type of connection	With screw terminals
--------------------	----------------------

Sustainability

Halogen free	Yes
--------------	-----

RoHS conform	Yes
--------------	-----

WBSEV1

