



dr424f4

**Din rail board, 4 row 96M, non-transparent door, flush**

**Technical Features**

**Voltage**

Nominal voltage	415 - 415 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Flush mounting

**Power**

Maximum power loss per cabinet at $\Delta T=20K$	36.22 W
--	---------

**Equipment**

Number of rails	4
Number of rows	4
With lock	No
Has neutral terminal block	Yes

**Capacity**

Number of modules	96
Number of half modules terminals per rail	48

**Functions**

Has protection main switch	No
With conduit inlets	Yes

**Dimensions**

Height	799 mm
Width	572.40 mm
Depth	110 mm
Built-in height	770 mm
Built-in width	590 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Built-in depth	110 mm
----------------	--------

**Cover, door**

Number of locks	0
-----------------	---

**Dimensions**

Number of width units	24
-----------------------	----

**Cover, door**

Door/cover is transparent	No
Cabinet door type	Single door

**Connection**

Number of conduit inlets	17
--------------------------	----

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Materials**

Material	Steel
RAL code	9010
Colour	Grey white

**Equipment**

Has earthing terminal block	No
Has mounting plate	No

---

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP40
Locking type	Without lock
Glow wire test	960 °C
Protection class with door	IP40

**Sustainability**

---

REACH-SVHC free	Yes
-----------------	-----